


Portal liniar DHSL-1-DGC18-DGSL10

Cod: 574499

FESTO

Pentru a obtine o oferta, va rugam apasati simbolul cerere FAX.



Fisa tehnica

Caracteristica	valoare
Asamblare	Portal 1
Incarcatura efectiva	0 ... 1 kg
Unitate de actionare, axa Z	DGSL-10
Sistem de actionare, axa Z	pneumatic
Cursa, axa Z	0 ... 200 mm
Acuratete de repetare in pozitia de capat, axa Z	$\pm 0,01$ mm
Unitate de actionare, axa Y	DGC-18
Sistem de actionare, axa Y	pneumatic
Pozitie intermediara, axa Y	x 1
Cursa, axa Y	0 ... 3.000 mm
Acuratete de repetare in pozitia de capat, axa Y	$\pm 0,02$ mm