

Bobina VACC-S18-120-K4-7-NM4ME

Cod: 8118175

FESTO



Fisa tehnica

| Caracteristica | valoare |
|--|---------------------------------------|
| tip de actionare | electric |
| pozitie instalare | Oricare |
| Afisarea pozitiei de comutare | nu |
| Durata de anclansare | 100 % |
| Clasa izolatie | H |
| Caracteristica bobina | 48 V DC: 12 W |
| Oscilatii admisibile ale tensiunii | -15 % / +10 % |
| Certificat ATEX in afara UE | EPL Db (BR) EPL Gb (BR) |
| Departament eliberare certificate | INMETRO DNV 19.0135X |
| Tip gaz cu protectie la explozie si aprindere | Ex eb mb IIC T4 Gb |
| Tip praf cu protectie la aprindere si explozie | Ex tb IIIC T120°C Db |
| Protectie la explozie temperatura ambientala | T4, T120°C: -25°C ≤ Ta ≤ +40°C |
| Conformitatea PWIS | VDMA24364-zona III |
| Tip de protectie | IP66 |
| Greutate produs | 580 g |
| Conectare electrica | Cutie terminal, cablu filetat M20x1.5 |
| Indicatie material | conform RoHS |