

Bobina VACC-S18-35-K4-3U-NE4ME

Cod: 8118254

FESTO



Fisa tehnica

Caracteristica	valoare
tip de actionare	electric
pozitie instalare	Oricare
Afisarea pozitiei de comutare	nu
Durata de anclansare	100 %
Clasa izolatie	H
Caracteristica bobina	230 V AC: 50/60 Hz, putere: 3.5 VA 230 V DC: 3.5 W
Oscilatii admisibile ale tensiunii	-15 % / +10 %
Certificat ATEX in afara UE	EPL Db (CN) EPL Gb (CN)
Departament eliberare certificate	GYJ17.1237X
Tip gaz cu protectie la explozie si aprindere	Ex e mb IIC T5/T6 Gb
Tip praf cu protectie la aprindere si explozie	Ex tD A21 IP66 T95°C/T80°C
Protectie la explozie temperatura ambientala	T5,T95°C: -25°C <= Ta <= +60°C T6,T80°C: -25°C <= Ta <= +50°C
Conformitatea PWIS	VDMA24364-zona III
Tip de protectie	IP66
Greutate produs	580 g
Conectare electrica	Cutie terminal, cablu filetat M20x1.5
Indicatie material	conform RoHS