

# Reductor EMGA-40-P-G8-EAS-40

Cod: 8141729

FESTO



## Fisa tehnica

Caracteristica	valoare
Transmisie flansa	40 mm
Motor cu flansa	40 mm
Joc de rasucire	0,25 deg
tipul reductorului	Angrenaj planetar
Raport de transmisie	8:1
Viteza maxima de intrare	18.000 1/min
Temperatura de operare reductor	-25 ... 90 °C
Conformitatea PWIS	VDMA24364-B2-L
Tip de protectie	IP54
Cuplu de actionare continua	6 Nm
Momentul de inertie al angrenajului	0,015 kgcm <sup>2</sup>
Cuplu maxim iesire	10 Nm
Eficienta maxima	96 %
rigiditate la torsiune	0,85 Nm/arcmin
Greutate produs	350 g
Interfata reductor arbore de iesire	40G
Interfata reductor arbore de antrenare	40P
Indicatie material	conform RoHS