


Reductor EMGA-120-P-G12-SAS-100

Cod: 8141754

FESTO



Fisa tehnica

Caracteristica	valoare
Transmisie flansa	120 mm
Motor cu flansa	100 mm
Joc de rasucire	0,15 deg
tipul reductorului	Angrenaj planetar
Raport de transmisie	12:1
Viteza maxima de intrare	6.500 1/min
Temperatura de operare reductor	-25 ... 90 °C
Conformitatea PWIS	VDMA24364-B2-L
Tip de protectie	IP54
Cuplu de actionare continua	260 Nm
Momentul de inertie al angrenajului	2,224 kgcm ²
Cuplu maxim iesire	416 Nm
Eficienta maxima	96 %
rigiditate la torsiune	22 Nm/arcmin
Greutate produs	8.000 g
Interfata reductor arbore de iesire	120G
Interfata reductor arbore de antrenare	100A
Indicatie material	conform RoHS