

# Reductor EMGA-60-P-G8-SST-57

Cod: 8141764

FESTO



## Fisa tehnica

Caracteristica	valoare
Transmisie flansa	60 mm
Motor cu flansa	57 mm
Joc de rasucire	0,17 deg
tipul reductorului	Angrenaj planetar
Raport de transmisie	8:1
Viteza maxima de intrare	13.000 1/min
Temperatura de operare reductor	-25 ... 90 °C
Conformitatea PWIS	VDMA24364-B2-L
Tip de protectie	IP54
Cuplu de actionare continua	18 Nm
Momentul de inertie al angrenajului	0,067 kgcm <sup>2</sup>
Cuplu maxim iesire	29 Nm
Eficienta maxima	97 %
rigiditate la torsiune	2,4 Nm/arcmin
Greutate produs	900 g
Interfata reductor arbore de iesire	60G
Interfata reductor arbore de antrenare	57A
Indicatie material	conform RoHS