


Reductor EMGA-80-P-G8-SST-87

Cod: 8141766

FESTO



Fisa tehnica

Caracteristica	valoare
Transmisie flansa	80 mm
Motor cu flansa	87 mm
Joc de rasucire	0,12 deg
tipul reductorului	Angrenaj planetar
Raport de transmisie	8:1
Viteza maxima de intrare	7.000 1/min
Temperatura de operare reductor	-25 ... 90 °C
Conformitatea PWIS	VDMA24364-B2-L
Tip de protectie	IP54
Cuplu de actionare continua	50 Nm
Momentul de inertie al angrenajului	0,37 kgcm ²
Cuplu maxim iesire	80 Nm
Eficienta maxima	97 %
rigiditate la torsiune	8,4 Nm/arcmin
Greutate produs	2.100 g
Interfata reductor arbore de iesire	80G
Interfata reductor arbore de antrenare	87A
Indicatie material	conform RoHS