

# 氣條

## VABM-C8-12E-G14-4-PT-L

料號: 1247975

Classic - nicht für Neukonstruktionen verwenden

Modern alternatives can be found by entering the first four characters of the type code in the search field.

FESTO



### 技術參數

特性	值
網柵尺寸	12 mm
閥位的最大數量	4
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
耐腐蝕等級 CRC	0 - No corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
最大緊固扭矩, 閥安裝	0.6 Nm
最大緊固扭矩, 牆面安裝	5 Nm
產品重量	521 g
氣壓連接, 氣口 1	G1/4
氣壓連接, 氣口 3	G1/4
氣壓連接, 氣口 5	G1/4
材料備註	符合 RoHS
Material manifold	鍛造鋁合金