


# L型快插式螺紋接頭,長

## QSL-L-G1/8-8-100

料號: 133017

FESTO

360° orientable, male thread with external hexagon.



### 技術參數

| 特性  | 值  |
|---|--|
| 尺寸  | 標準   |
| 額定尺寸  | 6 mm   |
| 柱頭螺栓上的密封件類型                                     | 密封圈  |
| 裝配位置  | 任何   |
| 設計  | L-shape, long  |
| 容器尺寸  | 100  |
| 設計結構  | 推/拉原理  |
| Operating pressure for entire temperature range | -0.095 ... 0.6 MPa   |
| 操作壓力的完整溫度範圍                                     | -0.95 ... 6 bar  |
| Operating pressure for entire temperature range | -13.775 ... 87 psi   |
| Temperature-dependent operating pressure        | -0.095 ... 1.4 MPa   |
| 溫度取決於操作壓力                                       | -0.95 ... 14 bar   |
| Temperature-dependent operating pressure        | -13.775 ... 203 psi  |
| Maritime classification                         | see certificate  |
| 操作介質  | 壓縮空氣符合 ISO8573-1:2010 [7:-:-]<br>Water as per manufacturer's declaration at <a href="http://www.festo.com">www.festo.com</a> |
| 注意: 操作和嚮導介質                                     | 潤滑操作可行   |
| 耐腐蝕等級 CRC                                       | 1 - Low corrosion stress   |
| PWIS conformity                                 | VDMA24364-B1/B2-L  |
| 環境溫度  | -10 ... 80 °C  |
| 額定鎖緊扭矩  | 7 Nm   |
| 額定擰緊扭矩公差  | ± 20 %   |
| 產品重量  | 17 g   |
| 安裝類型  | External hexagon A/F 13  |
| 氣壓連接, 氣口 1                                      | 外螺紋 G1/8   |
| 氣壓連接, 氣口 2                                      | For tubing outside diameter 8 mm   |
| 釋放環的顏色  | 藍色   |
| 材料備註  | 符合 RoHS  |
| Material housing                                | PBT  |
| Material release ring                           | POM  |
| Material of tubing seal                         | NBR  |
| Material of tube retaining claw                 | 高合金鋼, 耐腐蝕  |