

聯合螺栓 MCK-PK-9-KU

料號: 211293

FESTO

聚合物結構.



技術參數

特性	值
尺寸	內螺紋 M16x1
Operating pressure for entire temperature range	0 ... 1 MPa
操作壓力的完整溫度範圍	0 ... 10 bar
Operating pressure for entire temperature range	0 ... 145 psi
PWIS conformity	VDMA24364-B2-L
環境溫度	-10 ... 60 °C
氣壓連接, 氣口 1	用於倒鉤接頭內徑 9 mm 具螺母
Material of union nut	POM
材料備註	符合 RoHS