

# 塑料氣管 PUN-V0-10X1,5-GN

料號: 525448

FESTO

阻燃劑



## 技術參數

| 特性  | 值  |
|---|--|
| 外徑  | 10 mm  |
| 與流量相關的彎曲半徑                                      | 54 mm  |
| 內徑  | 7 mm   |
| 最小彎曲半徑  | 20 mm  |
| Tubing characteristics                          | Suitable for energy chains                                   |
| Operating pressure for entire temperature range | -0.095 ... 0.7 MPa   |
| 操作壓力的完整溫度範圍                                     | -0.95 ... 7 bar  |
| Operating pressure for entire temperature range | -13.775 ... 101.5 psi  |
| Temperature-dependent operating pressure        | -0.095 ... 1 MPa   |
| 溫度取決於操作壓力                                       | -0.95 ... 10 bar   |
| Temperature-dependent operating pressure        | -13.775 ... 145 psi  |
| 操作壓力注意事項  | Water: max. 0.6 MPa at max. 50 °C                            |
| 授權  | TÜV  |
| 認證核發部門  | B 013277 0506 00   |
| 操作介質  | 壓縮空氣符合 ISO8573-1:2010 [7:-:-]<br>Water (liquid, free of ice) |
| Material fire test                              | UL94 V-0 (3mm)<br>UL94 V-2 (0,75mm)                          |
| PWIS conformity                                 | VDMA24364-B2-L   |
| 環境溫度  | -35 ... 60 °C  |
| Note on ambient temperature                     | For unpressurised use up to 90 °C                            |
| 產品重量視長度而定                                       | 0.051 kg/m   |
| 氣壓連接  | For push-in connector outside diameter 10 mm                 |
| 顏色  | 綠色   |
| 關於顏色  | 由於高溫保護導致偏離標準色  |
| 肖氏硬度  | D 54 +/-3  |
| 材料備註  | 符合 RoHS  |
| Material tubing                                 | TPE-U(PU)  |