

塑料氣管 PAN-V0-12X1,5-WS

料號: 525481

FESTO

阻燃劑



技術參數

| 特性 | 值 |
|---|--|
| 外徑 | 14 mm |
| 插入式接頭的外徑 | 12 mm |
| 與流量相關的彎曲半徑 | 65 mm |
| 內徑 | 9 mm |
| 最小彎曲半徑 | 43 mm |
| Tubing characteristics | Suitable for energy chains |
| Operating pressure for entire temperature range | -0.095 ... 0.3 MPa |
| 操作壓力的完整溫度範圍 | -0.95 ... 3 bar |
| Operating pressure for entire temperature range | -13.775 ... 43.5 psi |
| Temperature-dependent operating pressure | -0.095 ... 1.2 MPa |
| 溫度取決於操作壓力 | -0.95 ... 12 bar |
| Temperature-dependent operating pressure | -13.775 ... 174 psi |
| 操作壓力注意事項 | Mineral oil: max. 0.3 MPa at max. 90°C Water: max. 0.3 MPa at max. 90°C |
| 操作介質 | 壓縮空氣符合 ISO8573-1:2010 [7:-:-] 礦物油 Water (liquid, free of ice) |
| Material fire test | UL94 V-0 (casing) |
| PWIS conformity | VDMA24364-B2-L |
| 環境溫度 | -30 ... 90 °C |
| 產品重量視長度而定 | 0.133 kg/m |
| 氣壓連接 | For push-in connector outside diameter 12 mm |
| 顏色 | 白色 |
| 肖氏硬度 | A 72 +/-4 D 57 +/-3 |
| 材料備註 | 符合 RoHS |
| Material tubing | 多醯胺 12 PVC-P |