

聯合螺栓 MCK-PK-4-KD

料號: 533673

FESTO

金屬結構.



技術參數

特性	值
尺寸	內螺紋 M10x1
Operating pressure for entire temperature range	-0.095 ... 1.2 MPa
操作壓力的完整溫度範圍	-0.95 ... 12 bar
Operating pressure for entire temperature range	-13.775 ... 174 psi
耐腐蝕等級 CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
環境溫度	-10 ... 60 °C
氣壓連接, 氣口 1	For tubing outside diameter 6 mm 用於倒鉤接頭內徑 4 mm 具螺母
Material of union nut	Wrought aluminium alloy, nickel-plated
材料備註	符合 RoHS