

## 電源電纜

### KPWR-MC-1-SUB-9HC-10

料號: 537933

將停止供貨的產品

適用於 MTR-DCI-...

FESTO



## 技術參數

特性	值
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	有角的
Electrical connection 1, connection type	插頭插座
Electrical connection 1, cable outlet	直的
Electrical connection 1, connection technology	Sub-D Mixed
Electrical connection 1, number of pins/wires	2
Electrical connection 1, occupied pins/wires	2
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	電纜
Electrical connection 2, connection technology	開放式終端
Electrical connection 2, number of pins/wires	2
Electrical connection 2, occupied pins/wires	2
工作電壓範圍 DC	24 ... 48 V
電纜長度	10 m
電纜屬性	適合於拖鏈
Bending radius, flexible cable installation	$\geq 64$ mm
電纜直徑	8.6 mm
電纜結構	2x1,5 已屏蔽
導體的額定截面	1.5 mm <sup>2</sup>
導線末端	Pin terminal
防護等級	IP54
Note on degree of protection	裝配狀態
環境溫度	0 ... 50 °C