


插頭插座, 具電纜

KMEB-3-24-2.5

料號: 547270

FESTO

用於電磁閥 VUVB, 具 24 V 線圈



技術參數

特性	值
裝配位置	任何
產品重量	120 g
電氣連接 1	Socket, to EN 175301-803, type C
Electrical connection 1, design	有角的
Electrical connection 1, connection type	插頭插座
Electrical connection 1, cable outlet	Angled
Electrical connection 1, note about the cable outlet	90°
Electrical connection 1, number of pins/wires	2
Electrical connection 1, type of mounting	通過M2.5中心螺絲安裝在電磁閥上
Electrical connection 2, connection technology	開放式終端
Electrical connection 2, number of pins/wires	2
額定工作電壓 DC	24 V
極性保護	用於所有電接口
保護性接地	還未上市
電纜長度	2.5 m
電纜屬性	標準
電纜直徑	5.2 mm
電纜結構	2x0,75
導線末端	導線末端套圈
防護等級	IP65 符合 IEC 60529
環境溫度	-20 ... 80 °C
CE 符號 (參見符合的標準)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
污染程度	3
耐腐蝕等級 CRC	1 - Low corrosion stress
Material cable sheath	PVC
Material housing	PC
Material seals	NBR
Material electrical contact	Silver-plated copper alloy