

塑料氣管 PEN-16X2,5-GN

料號: 551473

FESTO

標準外徑氣管, 用於QS插頭連接件, 聚乙烯 (不可用於食品行業)



技術參數

特性	值
外徑	16 mm
與流量相關的彎曲半徑	122 mm
內徑	10.8 mm
最小彎曲半徑	57.5 mm
Tubing characteristics	Suitable for energy chains in applications with higher cycle rates
Tubing test conditions	Suitability for energy chains: > 5 million cycles according to FN 942021
溫度取決於操作壓力	-0.95 ... 10 bar
授權	TÜV
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:-:-] Water as per manufacturer's declaration at www.festo.com
PWIS conformity	VDMA24364-B1/B2-L
環境溫度	-30 ... 60 °C
產品重量視長度而定	0.1029 kg/m
氣壓連接	For push-in connector outside diameter 16 mm
顏色	綠色
肖氏硬度	D 52 +/-3
材料備註	符合 RoHS
Material tubing	PE