


連接電纜

VMPAL-KMSK-S-SD25-IP67-

料號: 562394

FESTO



技術參數

特性	值
電氣連接	具插頭電纜
電纜屬性	Suitable for energy chains
電纜的最小彎折半徑	63 mm
電纜直徑	12.5 mm
電纜結構	25x0,34
防護等級	IP67 符合 IEC 60529
Ambient temperature with flexible cable installation	-5 ... 80 °C
CE 符號 (參見符合的標準)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B1/B2-L
材料備註	符合 RoHS
耐腐蝕等級 CRC	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PU)