

# 塑料氣管

## PEN-3/16-SW-150-CB

料號: 569882

FESTO

標準外徑氣管, 用於QS插頭連接件, 聚乙烯 (不可用於食品行業)



### 技術參數

特性	值
外徑, 英寸	3/16
與流量相關的彎曲半徑	0.075 ft
最小彎曲半徑	0.039 ft
Tubing characteristics	Suitable for energy chains in applications with higher cycle rates
Tubing test conditions	Suitability for energy chains: > 5 million cycles according to FN 942021
溫度取決於操作壓力	-14.4 ... 145 Psi
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:-:-] Water as per manufacturer's declaration at <a href="http://www.festo.com">www.festo.com</a>
PWIS conformity	VDMA24364-B1/B2-L
環境溫度	-22 ... 140 °F
產品重量視長度而定	0.1 oz/ft
氣壓連接	For push-in connector outside diameter 3/16"
顏色	黑色
肖氏硬度	D 52 +/-3
材料備註	符合 RoHS
Material tubing	PE