

塑料氣管

PUN-V0-16X2,5-BL-C

料號: 570354

FESTO

阻燃劑



技術參數

| 特性 | 值 |
|---|--|
| 外徑 | 16 mm |
| 與流量相關的彎曲半徑 | 90 mm |
| 內徑 | 11 mm |
| 最小彎曲半徑 | 50 mm |
| Tubing characteristics | Suitable for energy chains |
| Operating pressure for entire temperature range | -0.095 ... 0.7 MPa |
| 操作壓力的完整溫度範圍 | -0.95 ... 7 bar |
| Operating pressure for entire temperature range | -13.775 ... 101.5 psi |
| Temperature-dependent operating pressure | -0.095 ... 1 MPa |
| 溫度取決於操作壓力 | -0.95 ... 10 bar |
| Temperature-dependent operating pressure | -13.775 ... 145 psi |
| 操作壓力注意事項 | Water: max. 0.6 MPa at max. 50 °C |
| 授權 | TÜV |
| 認證核發部門 | B 013277 0506 00 |
| 操作介質 | 壓縮空氣符合 ISO8573-1:2010 [7:-:-] Water (liquid, free of ice) |
| Material fire test | UL94 V-0 (3mm) UL94 V-2 (0,75mm) |
| PWIS conformity | VDMA24364-B2-L |
| 環境溫度 | -35 ... 60 °C |
| Note on ambient temperature | For unpressurised use up to 90 °C |
| 產品重量視長度而定 | 0.147 kg/m |
| 氣壓連接 | For push-in connector outside diameter 16 mm |
| 顏色 | 藍色 |
| 關於顏色 | 由於高溫保護導致偏離標準色 |
| 肖氏硬度 | D 54 +/-3 |
| 材料備註 | 符合 RoHS |
| Material tubing | TPE-U(PU) |