

堵頭 NPQH-P-S4-P10

料號: 578257

FESTO



技術參數

特性	值
尺寸	標準
裝配位置	任何
設計	Blanking plug
容器尺寸	10
Operating pressure for entire temperature range 操作壓力的完整溫度範圍	-0.095 ... 2 MPa -0.95 ... 20 bar
Operating pressure for entire temperature range 操作壓力注意事項	-13.775 ... 290 psi Water: max. 0.6 MPa at 0 - 50 °C
認證核發部門	NSF C0523185
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:-:-] Water (liquid, free of ice)
注意: 操作和嚮導介質	潤滑操作可行
耐腐蝕等級 CRC	3 - High corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
無塵室等級	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Food-safe	See declaration of conformity NSF/ANSI 169
環境溫度	0 ... 150 °C
產品重量	2.3 g
氣壓連接, 氣口 1	Push-in sleeve diameter 4 mm
材料備註	符合 RoHS
Material housing	Brass, chemically nickel-plated