

堵頭 NPQH-P-S8-P10

料號: 578259

FESTO



技術參數

| 特性 | 值 |
|--|--|
| 尺寸 | 標準 |
| 裝配位置 | 任何 |
| 設計 | Blanking plug |
| 容器尺寸 | 10 |
| Operating pressure for entire temperature range 操作壓力的完整溫度範圍 | -0.095 ... 2 MPa -0.95 ... 20 bar |
| Operating pressure for entire temperature range 操作壓力注意事項 | -13.775 ... 290 psi Water: max. 0.6 MPa at 0 - 50 °C |
| 認證核發部門 | NSF C0523185 |
| 操作介質 | 壓縮空氣符合 ISO8573-1:2010 [7:-:-] Water (liquid, free of ice) |
| 注意: 操作和嚮導介質 | 潤滑操作可行 |
| 耐腐蝕等級 CRC | 3 - High corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| 無塵室等級 | This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly. |
| Food-safe | See declaration of conformity NSF/ANSI 169 |
| 環境溫度 | 0 ... 150 °C |
| 產品重量 | 7.4 g |
| 氣壓連接, 氣口 1 | Push-in sleeve diameter 8 mm |
| 材料備註 | 符合 RoHS |
| Material housing | Brass, chemically nickel-plated |