


插入接頭

QS-G3/4-22

料號: 8040613

FESTO



技術參數

特性	值
尺寸	標準
額定尺寸	20 mm
柱頭螺柱上的密封件類型	密封圈
裝配位置	任何
設計	直式結構
容器尺寸	1
設計結構	推/拉原理
Operating pressure for entire temperature range	-0.095 ... 1.4 MPa
操作壓力的完整溫度範圍	-0.95 ... 14 bar
Operating pressure for entire temperature range	-13.775 ... 203 psi
Temperature-dependent operating pressure	-0.095 ... 1.4 MPa
溫度取決於操作壓力	-0.95 ... 14 bar
Temperature-dependent operating pressure	-13.775 ... 203 psi
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:-:-] Water as per manufacturer's declaration at www.festo.com
注意: 操作和嚮導介質	潤滑操作可行
耐腐蝕等級 CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
環境溫度	-20 ... 80 °C
額定鎖緊扭矩	20 Nm
額定擰緊扭矩公差	± 20 %
產品重量	93.2 g
安裝類型	External hexagon A/F 32
氣壓連接, 氣口 1	外螺紋 G3/4
氣壓連接, 氣口 2	For tubing outside diameter 22 mm
釋放環的顏色	藍色
材料備註	符合 RoHS
Material housing	鍍鎳黃銅
Material release ring	POM
Material of tubing seal	NBR
Material of tube retaining claw	高合金鋼, 耐腐蝕