

塑料氣管
PTFEN-6X1-NT-100
 料號: 8061172



技術參數

特性	值
外徑	6 mm
與流量相關的彎曲半徑	40 mm
內徑	4 mm
最小彎曲半徑	38 mm
Instructions for use	Tubing without printing
Operating pressure for entire temperature range	-0.095 ... 0.5 MPa
操作壓力的完整溫度範圍	-0.95 ... 5 bar
Operating pressure for entire temperature range	-13.775 ... 72.5 psi
Temperature-dependent operating pressure	-0.095 ... 1.5 MPa
溫度取決於操作壓力	-0.95 ... 15 bar
Temperature-dependent operating pressure	-13.775 ... 217.5 psi
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:-:-]
Material fire test	UL94 V-0
PWIS conformity	VDMA24364-B1/B2-L
無塵室等級	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Food-safe	See Supplementary material information
環境溫度	-20 ... 150 °C
產品重量視長度而定	0.034 kg/m
氣壓連接	For push-in connector outside diameter 6 mm For barbed connector outside diameter 6 mm with union nut 用於倒鉤接頭內徑 4 mm 具螺母 用於倒鉤接頭內徑 4 mm
顏色	中性
肖氏硬度	D 55 +/-5
材料備註	符合 RoHS
Material tubing	PTFE