

真空過濾器 OAFF-G3-5

料號: 8068944

FESTO



技術參數

| 特性 | 值 |
|---------------------------------|------------------------------|
| 過濾等級 | 40 µm |
| 容器尺寸 | 10 |
| Operating pressure MPa | -95 ... 0 kPa |
| 操作壓力 | -0.95 ... 0 bar |
| Operating pressure | -13.775 ... 0 psi |
| 操作介質 | 大氣基於 ISO 8573-1:2010 [7:-:-] |
| PWIS conformity | VDMA24364-B1/B2-L |
| 產品重量 | 1 g |
| 安裝類型 | 插上式 偵測 |
| 材料備註 | 符合 RoHS |
| Material filter | 網孔 PA |
| Material housing | POM |
| Ejector pulse suitability | 0.7 MPa |
| 噴射脈衝適用性 | 7 bar |
| Ejector pulse suitability (psi) | 101.5 psi |