

linear gantry YXML-2

料號: 8082250

FESTO



技術參數

特性	值
Required flatness of the mounting surfaces	0.1 mm/m
裝配位置	水平
設計結構	Linear gantry system with electric drive modules
循環功率	100 %
PWIS conformity	VDMA24364 zone III
儲藏溫度	-10 ... 60 °C
相對空氣濕度	0 - 90 %
環境溫度	10 ... 40 °C
Maintenance interval	2,500 km
材料備註	符合 RoHS
Material adapter plate	Anodised aluminium
Material mounting bracket	高合金鋼, 耐腐蝕
Material energy chains	PA-加強