


Y型插入接頭 NPQR-Y-Q8-E

料號: 8085725

FESTO



技術參數

特性	值
尺寸	標準
Tubing insertion depth	17 mm
裝配位置	任何
設計	Y-shape
容器尺寸	1
設計結構	推/拉原理
Operating pressure for entire temperature range	-0.095 ... 1.6 MPa
操作壓力的完整溫度範圍	-0.95 ... 16 bar
Operating pressure for entire temperature range	-13.775 ... 232 psi
操作壓力注意事項	Water: max. 0.7 MPa at 0 - 80°C
認證核發部門	NSF C0556009
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:-:-] Water (liquid, free of ice)
注意: 操作和嚮導介質	潤滑操作可行
耐腐蝕等級 CRC	4 - Very high corrosion stress
PWIS conformity	VDMA24364-B2-L
RSBP classification to CD-0033	F1a
無塵室等級	ISO class 4
Food-safe	See declaration of conformity NSF/ANSI 169
環境溫度	-20 ... 150 °C
產品重量	37.8 g
氣壓連接, 氣口 1	For tubing outside diameter 8 mm
氣壓連接, 氣口 2	For tubing outside diameter 8 mm
材料備註	符合 RoHS
Material housing	高合金鋼, 耐腐蝕
Guard ring material	高合金鋼, 耐腐蝕
Material release ring	高合金鋼, 耐腐蝕
Material of tubing seal	FPM
Material of tube retaining claw	高合金鋼, 耐腐蝕
Thrust ring material	PPSU