

dosing needle set VAVN-N-A1.6-12-30-V1-P10

料號: 8104291

FESTO



技術參數

| 特性 | 值 |
|---|--|
| 容器尺寸 | 10 |
| Dosing needle outside diameter | 1.6 mm |
| Length of dosing needle | 30 mm |
| Nominal width of dosing needle | 1.2 mm |
| 耐腐蝕等級 CRC | 3 - High corrosion stress |
| PWIS conformity | VDMA24364 zone III |
| Food-safe | See Supplementary material information |
| Fluid connection | Terminal connection |
| 介質 | 流體介質 氣態介質 |
| Note on the medium | Observe resistance of materials that come into contact with media Maximum particle size: 5 µm |
| Operating pressure MPa | 0 ... 0.4 MPa |
| 操作壓力 | 0 ... 4 bar |
| 標準額定流量 | 20.19 l/min |
| Information on standard nominal flow rate | In case of a pressure drop of 1 -> 0 bar (gaseous media) |
| 流量 Kv | 0.039 m3/h |
| Information on flow rate Kv | For water as medium |
| 介質溫度 | 5 ... 60 °C |
| 環境溫度 | 5 ... 60 °C |
| 儲藏溫度 | -20 ... 70 °C |
| 裝配位置 | 任何 |
| 產品重量 | 2.1 g |
| 材料備註 | 符合 RoHS |
| Material of dosing needle | 高合金鋼, 耐腐蝕 |
| Material number of dosing needle | 1.4404 |
| 材料與介質接觸 | 高合金鋼, 耐腐蝕 |