

堵頭  
NPQE-P-S6-P10  
料號: 8113205

FESTO



技術參數

特性	值
尺寸	標準
裝配位置	任何
設計	Blanking plug
容器尺寸	10
Operating pressure for entire temperature range	-0.095 ... 0.8 MPa
操作壓力的完整溫度範圍	-0.95 ... 8 bar
Operating pressure for entire temperature range	-13.775 ... 116 psi
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:4:4]
注意: 操作和嚮導介質	潤滑操作可行
耐腐蝕等級 CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364 zone III
無塵室等級	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
環境溫度	-5 ... 60 °C
產品重量	0.9 g
氣壓連接, 氣口 1	Push-in sleeve diameter 6 mm
釋放環的顏色	藍色
材料備註	符合 RoHS
Material housing	PBT
Material release ring	POM