

雙氣嘴

NPFC-DS-G14-G38-M

料號: 8142586

FESTO



技術參數

特性	值
Material threaded fitting	Nickel-plated brass
容器尺寸	10
操作壓力	-0.95 ... 10 bar
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:8:4]
耐腐蝕等級 CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
環境溫度	-10 ... 60 °C
Nominal tightening torque, pneumatic connection 1	38.5 Nm
Nominal tightening torque, pneumatic connection 2	9.05 Nm
額定擰緊扭矩公差	± 20 %
產品重量	23.13 g
氣壓連接, 氣口 1	G3/8
氣壓連接, 氣口 2	G1/4
材料備註	符合 RoHS
Material seals	PVC