

接頭組件

DADG-AK-G8-12-20

料號: 8152374

FESTO



技術參數

| 特性 | 值 |
|-----------------------------|-------------------------------|
| 尺寸 | 12 |
| 行程 | 20 mm |
| Operating pressure MPa | 0.1 ... 0.8 MPa |
| 操作壓力 | 1 ... 8 bar |
| Operating pressure | 14.5 ... 116 psi |
| 操作介質 | 壓縮空氣符合 ISO8573-1:2010 [7:4:4] |
| 耐腐蝕等級 CRC | 1 - Low corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| 環境溫度 | -10 ... 60 °C |
| 最大緊固扭矩 | 1.5 Nm |
| Tightening torque tolerance | ± 10 % |
| 最大的緊固扭矩, 氣接口 1 | 0.7 Nm |
| 產品重量 | 12.9 g |
| 氣壓連接 | M5 |
| Material adapter | 環氧樹脂 |
| Material seals | NBR |
| Material screws | Coated steel |