

密封圈

OL-M7

料號: 8153155

FESTO



技術參數

特性	值
基於標準	ISO 16030
Operating pressure for entire temperature range	-0.095 ... 3 MPa
操作壓力的完整溫度範圍	-0.95 ... 30 bar
Operating pressure for entire temperature range	-13.775 ... 435 psi
耐腐蝕等級 CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
環境溫度	-40 ... 100 °C
環境溫度下手動緊固	是
額定鎖緊扭矩	3 Nm
額定擰緊扭矩公差	± 20 %
產品重量	0.1 g
氣壓連接	M7
材料備註	符合 RoHS
Material stops	鋁
Material seals	HNBR