


pressure gauge PAGL-HP3-63-60-G14

Part number: 1166938

FESTO



Data sheet

Feature	Value
Indicating range [bar]	0 ... 60 bar
Display range	0 ... 6 MPa 0 ... 870 psi
Conforms to standard	EN 837-1
Nominal size of pressure gauge	63
Design structure	Bourdon-tube pressure gauge
Mounting type	Line installation
Operating medium	Inert gases Neutral fluids
Operating pressure MPa	0 ... 6 MPa
Operating pressure	0 ... 60 bar 0 ... 870 psi
Alternating load factor	0.66
Measurement accuracy class	1,6
Protection class	IP65
Storage temperature	-40 ... 70 °C
Medium temperature	0 ... 60 °C
Ambient temperature	0 ... 60 °C
Materials note	Conforms to RoHS
Position of connection	Rear side central
Pneumatic connection	G1/4
Materials in contact with media	Brass
Material of threaded plug	Brass
Material housing	Steel
Material screen	PS
Housing colour	silver
Product weight	80 g
Note on operating and pilot medium	No acetylene No oxygen
Scale	Triple scale Bar (external) MPa (outer scale) psi (inner)