



Solenoid valve JMUH-5/2-D-2C-VI

Part number: 120359

FESTO

For valve terminal

Products to be discontinued. Available until 2011.



Data sheet

Feature	Value
Valve function	5/2 monostable
Width	54 mm
Operating pressure	-0.9 ... 16 bar
Design structure	Piston slide
Type of reset	mechanical spring
Nominal size	13.5 mm
Sealing principle	soft
Manual override	Pushing
Type of piloting	direct
Flow direction	reversible
Operating medium	Filtered, unlubricated compressed air, 50 µm filtration Filtered, lubricated compressed air, 50 µm filtration
Medium temperature	-5 ... 50 °C
Ambient temperature	-5 ... 50 °C
Mounting type	with through hole
Pneumatic connection, port 1	Connection plate size 2 as per ISO 5599-2
Pneumatic connection, port 2	Connection plate size 2 as per ISO 5599-2
Pneumatic connection, port 3	Sub-base
Pneumatic connection, port 4	Connection plate size 2 as per ISO 5599-2
Pneumatic connection, port 5	Sub-base