



# silencer AMTE-M-LH-G34

Part number: 1205864

FESTO

Suitable for reducing noise at the exhaust ports of pneumatic systems.



## Data sheet

Feature	Value
Assembly position	Any
Container size	10
Operating pressure MPa	0 ... 1 MPa
Operating pressure	0 ... 10 bar
Flow rate to atmosphere	12,400 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Sound pressure level	85 dB(A)
Ambient temperature	-40 ... 80 °C
Product weight	80 g
Pneumatic connection	G3/4
Material of silencer insert	Bronze
Material of threaded plug	Brass
Materials note	Conforms to RoHS