


parallel kit EAMM-U-50-S38-42A-78

Part number: 1217945

★ Core product range

Suitable for electric drives.

FESTO



Data sheet

| Feature | Value |
|--------------------------|------------------------|
| Size | 50 |
| Assembly position | Any |
| Gear unit ratio | 1:1 |
| Max. speed | 6,000 1/min |
| PWIS conformity | VDMA24364 zone III |
| Storage temperature | -25 ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Protection class | IP40 |
| Ambient temperature | -10 ... 60 °C |
| Mass moment of inertia | 12.1 kgmm ² |
| No-load driving torque | 0.01 Nm |
| Transferable torque | 1 Nm |
| Product weight | 590 g |
| Interface code, actuator | S38 |
| Interface code, motor in | 42A |
| Materials note | Conforms to RoHS |