

# manifold rail

## VABM-C8-12E-G14-35-PT-L

Part number: 1247987

FESTO



### Data sheet

Feature	Value
Grid dimension	12 mm
Max. number of valve positions	35
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Max. tightening torque, valve mounting	0.6 Nm
Max. tightening torque, wall mounting	5 Nm
Product weight	2,138 g
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 3	G1/4
Pneumatic connection, port 5	G1/4