



HGL-1/2

Non-return valve

Feature	Data/description
Assembly position	Any
Valve function	piloted non-return function
Operating pressure	0,2 - 10 bar
Standard nominal flow rate	1.540 l/min
Switching time off	17 ms
Switching time on	8 ms
Operating medium	Dried, filtered compressed air Dried, filtered and lubricated compressed air
Medium temperature	-20 - 80 °C
Ambient temperature	-20 - 80 °C
Max. tightening torque	70 Nm
Mounting type	Threaded
Pilot air port 21	G1/2
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 2	G1/2
Materials information for screw-in stud	Aluminium
Materials information for seals	NBR