


Push-in Y-connector QSY-8H

Part number: 130630

★ Standard product range

with push-in sleeve.

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal size	4.6 mm
Assembly position	Any
Container size	10
Design structure	Push/pull principle
Temperature dependent operating pressure	-0.95 ... 14 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-] Water as per manufacturer's declaration at www.festo.com
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1
Ambient temperature	-10 ... 80 °C
Authorisation	Germanischer Lloyd
Product weight	13 g
Number of outputs	2
Number of supply lines	1
Pneumatic connection, supply line	Push-in sleeve QS-8
Pneumatic connection, output	für Schlauch Außen-Ø 8 mm
Colour of release ring	blue
Materials note	Conforms to RoHS
Materials information, housing	PBT
Release ring material data	POM
Materials information for tubing seal	NBR
Hose clamping segment material data	High alloy steel, non-corrosive