

**cartridge**  
**QSPK18-5/32-U**  
 Part number: 132171

**FESTO**

With push-in connector, straight



## Data sheet

Feature	Value
Size	Mini
Nominal size	2.3 mm
Assembly position	Any
Container size	10
Design structure	Push/pull principle
Operating pressure complete temperature range	-0.95 ... 10 bar
Maritime classification	see certificate
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1 - Low corrosion stress
Ambient temperature	-5 ... 60 °C
Product weight	2.8 g
Pneumatic connection, port 1	QSP...18
Pneumatic connection, port 2	for tubing, 5/32" outside diameter
Colour of release ring	Grey
Materials note	Conforms to RoHS
Material housing	PA-reinforced
Material release ring	POM
Material of tubing seal	NBR
Material of tube retaining claw	High alloy steel, non-corrosive