


axial kit EAMM-A-D40-70A-S1

Part number: 1322185

FESTO

Suitable for electric drives.



Data sheet

Feature	Value
Assembly position	Any
PWIS conformity	VDMA24364 zone III
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP65
Ambient temperature	-10 ... 60 °C
Transferable torque	12.5 Nm
Product weight	410 g
Interface code, actuator	D40A D40B
Interface code, motor in	70A
Materials note	Conforms to RoHS