

Push-in Y-fitting NPQP-Y-R38-Q12

Part number: 132469

FESTO

Type to be discontinued. Available until 2013.



Data sheet

Feature	Value
Size	Standard
Nominal size	6.2 mm
Design structure	Push/pull principle
Temperature dependent operating pressure	-0.95 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	4
Ambient temperature	-20 ... 60 °C
Product weight	28 g
Pneumatic connection, port 1	R3/8
Pneumatic connection, port 2	for tubing, 12mm outside diameter
Materials note	Contains PWIS substances Conforms to RoHS
Materials information, housing	PP
Hose clamping segment material data	High alloy steel, non-corrosive