

plastic tubing

PUN-H-2X0,4-SW

Part number: 133039

FESTO

Approved for use in food processing (hydrolysis resistant)



Data sheet

| Feature | Value |
|-------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Outside diameter | 2 mm |
| Bending radius relevant for flow rate | 8 mm |
| Inside diameter | 1.2 mm |
| Min. bending radius | 5 mm |
| Instructions for use | TPE-U Ether basiert |
| Tubing characteristics | Suitable for energy chains |
| Operating pressure for entire temperature range | -0.095 ... 0.6 MPa |
| Operating pressure complete temperature range | -0.95 ... 6 bar |
| Operating pressure for entire temperature range | -13.775 ... 87 psi |
| Temperature-dependent operating pressure | -0.095 ... 1 MPa |
| Temperature dependent operating pressure | -0.95 ... 10 bar |
| Temperature-dependent operating pressure | -13.775 ... 145 psi |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| PWIS conformity | VDMA24364-B2-L |
| Cleanroom class | This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly. |
| Ambient temperature | -35 ... 60 °C |
| Product weight according to length | 0.0024 kg/m |
| Pneumatic connection | For push-in connector outside diameter 2 mm |
| Colour | Black |
| Shore hardness | D 52 +/- 3 |
| Materials note | Conforms to RoHS |
| Material tubing | TPE-U(PU) |