

Plastic tubing PU-2-BL

Part number: 13365

FESTO

For CN and CK connectors, particularly flexible and kink-resistant,
polyurethane (not approved for use in the food industry).
The maximum pressure value is permissible at the maximum temperature.



Data sheet

Feature	Value
Outside diameter	3.2 mm
Bending radius relevant for flow rate	13 mm
Inside diameter	2.3 mm
Temperature dependent operating pressure	-0.95 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Ambient temperature	-35 ... 60 °C
Authorisation	TÜV
Product weight according to length	0.005 kg/m
Colour	blue
Shore hardness	D 52 +/-3
Materials note	Free of copper and PTFE Conforms to RoHS
Materials information for tubing	TPE-U(PU)