



VAM-63-V1/0-1/4

Vacuum gauge

| Feature | Data/description |
|--------------------------------|--|
| Nominal size of pressure gauge | 63 |
| Position of connection | Rear side central |
| Design structure | Bourdon-tube pressure gauge |
| Indicating range [bar] | -1 - 0 bar |
| Indicating range [psi] | -14,5 - 0 psi |
| Operating medium | Compressed air, filtered, unlubricated Filtered, lubricated air |
| Continuous load factor | 0,75 |
| Alternating load factor | 0,67 |
| Ambient temperature | -10 - 60 °C |
| Measurement accuracy class | 1,6 |
| Mounting type | Threaded |
| Pneumatic connection | G1/4 |
| Materials information, housing | Steel Painted |
| Materials info, viewing window | Glass |