



# suction cup VASB-125-3/8-SI-B

Part number: 1387375

FESTO



## Data sheet

Feature	Value
Suction cup height compensator	25 mm
Nominal size	7 mm
suction cup diameter	125 mm
suction cup volume	307 cm <sup>3</sup>
Position of connection	on top
Assembly position	Any
Suction cup shape	Round, bellows 1.5 conv
Operating pressure MPa	-0.095 ... 0 MPa
Operating pressure	-0.95 ... 0 bar -13.775 ... 0 psi
Nominal operating pressure	-0.07 MPa -0.7 bar
Nominal operating pressure (psi)	-10.15 psi
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:-]
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364 zone III
Food-safe	See Supplementary material information
Ambient temperature	-40 ... 200 °C
Retention force at nominal operating pressure	610 N
Product weight	247 g
Mounting type	Via vacuum port
Vacuum connection	G3/8
Colour	transparent
Shore hardness	60 +/- 5
Material of threaded plug	Wrought Aluminium alloy
Materials note	Conforms to RoHS
Material suction cup	VMQ (silicon)