

barbed fitting CRCN-1/4-PK-4

Part number: 13972

FESTO

Corrosion resistant,
with sealing ring,
for plastic tubing PAN, PUN, PL, PP, PU.



Data sheet

Feature	Value
Nominal size	3.2 mm
Type of seal on screw-in stud	Sealing ring
Container size	1
Operating pressure complete temperature range	-0.95 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Food-safe	See Supplementary material information
Ambient temperature	0 ... 60 °C
Product weight	17.73 g
Pneumatic connection, port 1	Male thread G1/4
Pneumatic connection, port 2	For tubing outside diameter 6 mm
Materials note	Conforms to RoHS
Material housing	High alloy steel, non-corrosive
Material of threaded seal	PA-reinforced TPE-U(PU)