

barbed fitting CRCN-1/4-PK-6

Part number: 13973

FESTO

Corrosion resistant,
with sealing ring,
for plastic tubing PAN, PUN, PL, PP, PU.



Data sheet

| Feature | Value |
|---|---|
| Nominal size | 5.3 mm |
| Type of seal on screw-in stud | Sealing ring |
| Container size | 1 |
| Operating pressure complete temperature range | -0.95 ... 10 bar |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B2-L |
| Food-safe | See Supplementary material information |
| Ambient temperature | 0 ... 60 °C |
| Product weight | 16.5 g |
| Pneumatic connection, port 1 | Male thread G1/4 |
| Pneumatic connection, port 2 | For tubing outside diameter 8 mm |
| Materials note | Conforms to RoHS |
| Material housing | High alloy steel, non-corrosive |
| Material of threaded seal | PA-reinforced TPE-U(PU) |