



intermediate position module

DADM-EP-G6-10

Part number: 1492072

FESTO



Data sheet

Feature	Value
Size	10
Assembly position	Any
Design structure	guided motion sequence
Position detection	For proximity sensor
Operating pressure	3 ... 6 bar
Max. impact speed	0.8 m/s
Max. swivel time	150 ms
Repetition accuracy	±0,02 mm
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	0 ... 60 °C
Max. stop force	500 N
Product weight	154 g
Mounting type	With through-hole and centring sleeve
Pneumatic connection	M3
Materials note	Conforms to RoHS
Material seals	PU
Material housing	Wrought Aluminium alloy
Material lever	High alloy steel, non-corrosive