


adding counter PZA-A-B

Part number: 14992

FESTO



Data sheet

Feature	Value
Design structure	mechanical sequence counter with pneumatic drive
Type of reset	Pushbutton or pneumatic signal
Display	6-place
Release pressure, drive unit	0,2 ± 0,1 bar
Release pressure, return	0,15 ± 0,1 bar
Response pressure, drive unit	0,6 ± 0,2 bar
Response pressure, return	0,6 ± 0,2 bar
Operating pressure	2 ... 8 bar
Minimum reset pressure	2 bar
Minimum pulse length, drive unit	10 ms
Minimum pulse length, return	180 ms
Minimum pause period, drive unit	15 ms
Minimum pause period, return	50 ms
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation not possible
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 ... 60 °C
Product weight	155 g
Mounting type	with through hole
Pneumatic connection	M5
Material housing	ABS