

MSFG-24DC-EEX

Solenoid coil

Data sheet

Part no.: 150657

Page:1

Feature	Data/description
Solenoid system (dimensioning)	F
Minimum ambient temperature	-5 °C
Maximum ambient temperature	40 °C
Voltage type	DC
Nominal voltage	24 V
Power consumption (DC)	4,5 W
Duty cycle, solenoid	100 %
Degree of protection	IP65